

75 Liter Polypropylene Carboy, 120mm Cap - 12934

Product Images



Short Description

- Polypropylene construction allows for proper sterilization between uses
- Constructed from autoclavable USP Class VI, FDA grade materials
- Interchangeable caps and adapters provide top connection flexibility
- Rectangular ergonomic design saves valuable bench space

Description

These polypropylene (PP) carboys feature large handles and base with molded grip allowing you to easily lift and pour. The material type and volume are printed on the outside of the carboy along with large, easy-to-read metric graduation marks that are certified to $\pm 5\%$ accuracy. Available in 83-mm or 120-mm sizes, the included PP cap with platinum-cured silicone gasket provides a tight spill-proof seal. The larger 120-mm neck size allows you to reach into the carboy for quick and easy cleaning. Constructed from USP Class VI, FDA grade PP resin, the translucent carboys provide good chemical compatibility when using with various reagents, buffers, and powders.

Carboys are compatible with interchangeable caps and adapters. Select from a wide range of adapters with molded or quick connect hose barb configurations for top connection flexibility.

Recommended autoclave cycle: 15 PSI and 250 °F (121 °C) for 20 minutes.

Specifications

Model No	12934
UPC	697841181960
International Model No.	12934
Material Specifications	Polypropylene
Dimensions, Exterior	30" H x 14.4" W x 18.7" L
	762mm H x 366mm W x 475mm L
Capacity	19.8 gallon
Liter Capacity	75
Cap Size	120mm
Net Weight, lbs	14.0
Net Weight, kg	6.4