

10 Liter Polypropylene Carboy, With 3" Sanitary Neck - 12935

Product Images



Short Description

- Polypropylene construction allows for proper sterilization between uses
- Constructed from autoclavable USP Class VI, FDA grade materials
- Rectangular ergonomic design saves valuable bench space
- Three-inch sanitary neck comes without threads for easy cleaning

Description

These polypropylene (PP) carboys feature large handles and base with molded grip allowing you to easily lift and pour. The material type and volume are printed on the outside of the carboy along with large, easy-to-read metric graduation marks that are certified to $\pm 5\%$ accuracy. Constructed from USP Class VI, FDA grade PP resin, the translucent carboys provide good chemical compatibility when using with various reagents, buffers, and powders.

Recommended autoclave cycle: 15 PSI and 250 °F (121 °C) for 20 minutes.

Specifications

Model No	12935
UPC	697841181977
International Model No.	12935
Material Specifications	Polypropylene
Dimensions, Exterior	19.2" H x 6.4" W x 10.75" L 488mm H x 163mm W x 273mm L
Capacity	2.6 gallon
Liter Capacity	10
Net Weight, lbs	3.0
Net Weight, kg	1.4