

40 Liter Polypropylene Carboy, With 3" Sanitary Neck - 12937

Product Images



Short Description

- Polypropylene construction allows for proper sterilization between uses
- Constructed from autoclavable USP Class VI, FDA grade materials
- Rectangular ergonomic design saves valuable bench space
- Three-inch sanitary neck comes without threads for easy cleaning

Description

These polypropylene (PP) carboys feature large handles and base with molded grip allowing you to easily lift and pour. The material type and volume are printed on the outside of the carboy along with large, easy-to-read metric graduation marks that are certified to $\pm 5\%$ accuracy. Constructed from USP Class VI, FDA grade PP resin, the translucent carboys provide good chemical compatibility when using with various reagents, buffers, and powders.

Recommended autoclave cycle: 15 PSI and 250° F (121° C) for 20 minutes.

Specifications

Model No	12937
UPC	697841181991
International Model No.	12937
Material Specifications	Polypropylene
Dimensions, Exterior	29" H x 9.8" W x 17.1" L 737mm H x 249mm W x 434mm L
Capacity	10.6 gallon
Liter Capacity	40
Net Weight, lbs	9.0
Net Weight, kg	4.1