

# 10 Liter Polypropylene Carboy With Spigot, 83mm Cap - 12939

## Product Images

---



## Short Description

---

- Polypropylene construction allows for proper sterilization between uses
- Constructed from autoclavable USP Class VI, FDA grade materials
- Interchangeable caps and adapters provide top connection flexibility
- Rectangular ergonomic design saves valuable bench space

- Leakproof spigot includes easy-grip lever controlling two flow rates
- Leakproof spigot includes easy-grip lever controlling two flow rates

## Description

---

These polypropylene (PP) carboys feature large handles and base with molded grip allowing you to easily lift and pour. The material type and volume are printed on the outside of the carboy along with large, easy-to-read metric graduation marks that are certified to  $\pm 5\%$  accuracy. Available in 83-mm or 120-mm sizes, the included PP cap with platinum-cured silicone gasket provides a tight spill-proof seal. The larger 120-mm neck size allows you to reach into the carboy for quick and easy cleaning. Constructed from USP Class VI, FDA grade PP resin, the translucent carboys provide good chemical compatibility when using with various reagents, buffers, and powders.

Designed with internal threads and a hard stop to prevent over tightening and seal damage, leakproof polypropylene spigots feature 5/8- and 3/4-inch hose barbs, and a standard internal luer taper to fit a male barb adapter. Large lever controls two flow rates, one for continuous, locked flow and the other for a faster, manual flow. Carboys are compatible with interchangeable adapters and spigot fittings. Select from a wide range of adapters with molded or quick connect hose barb configurations for top connection flexibility, and additional spigots and versatile barbs for alternate bottom hosing connection options.

Recommended autoclave cycle: 15 PSI and 250 ° F (121 ° C) for 20 minutes.

Note: Length includes spigot.

## Specifications

---

Model No	12939
UPC	697841182011
International Model No.	12939
Material Specifications	Polypropylene
Dimensions, Exterior	19.5" H x 6.4" W x 13" L
	495mm H x 163mm W x 330mm L
Capacity	2.6 gallon
Liter Capacity	10
Cap Size	83mm
Net Weight, lbs	3.0
Net Weight, kg	1.4