

5 Liter Copolyester Carboy, 83mm Cap - 12947

Product Images



Short Description

- Constructed from a clear, BPA-free, USP Class VI, FDA grade resin
- Rectangular ergonomic design saves valuable bench space
- Interchangeable caps and adapters provide top connection flexibility
- Material, volume, and metric graduation marks imprinted on carboys

Description

- Constructed from a clear, BPA-free, USP Class VI, FDA grade resin
- Rectangular ergonomic design saves valuable bench space
- Interchangeable caps and adapters provide top connection flexibility
- Material, volume, and metric graduation marks imprinted on carboys

The ergonomic design on these copolyester (PETG) carboys features large handles and base with molded grip allowing you to easily lift and pour. The material type and volume are printed on the outside of the container along with large, easy-to-read clear metric graduation marks that are certified to $\pm 5\%$ accuracy. Available in 83-mm or 120-mm sizes, the included polypropylene cap with platinum-cured silicone gasket provides a tight spill-proof seal. The larger 120-mm neck size allows you to reach into the carboy for quick and easy cleaning. Constructed from USP Class VI, FDA grade PETG resin, the carboys provide moderate chemical compatibility when using with various reagents, buffers, solutions, and powders.

Carboys are compatible with interchangeable caps and adapters. Select from a wide range of adapters with molded or quick connect hose barb configurations for top connection flexibility.

Specifications

Model No	12947
UPC	697841182080
International Model No.	12947
Material Specifications	Copolyester
Dimensions, Exterior	16.3" H x 5.2" W x 8.7" L
	414mm H x 132mm W x 221mm L
Capacity	1.3 gallon
Liter Capacity	5
Net Weight, lbs	2.0
Net Weight, kg	0.9