
34" W x 16.875" D Wood Shelf With Clips for Laminate Corrosives Safety Cabinet 24140 - 24168

Product Images



Short Description

- Add function and convenience with additional shelves
- Wood shelf and clips
- Fits Cabinet Model No 24140

Description

Protect workers, reduce fire risks, and improve productivity by storing flammable fuels and chemicals in code-compliant safety cabinets. Designed to meet OSHA and NFPA standards, Sure-Grip[®] EX cabinets are constructed of sturdy 18-gauge (1-mm) thick double-wall, welded steel with 1-1/2" (38-mm) of insulating air space for fire resistance. High-performance, self-latching doors close easily and securely for maximum protection under fire conditions. Fail-safe closing mechanism ensures three-point stainless steel bullet latching system works every time.

For added security, U-Loc™ handle comes with a cylinder lock and key set or accepts an optional padlock. Haz-Alert™ reflective warning labels are highly visible under fire conditions or during power outages when illuminated with a flashlight.

Patented SpillSlope® galvanized steel shelves direct spills to back and bottom of a leakproof 2" (51-mm) bottom sump. They adjust on 3" (76-mm) centers for versatile storage. Cabinets also feature dual vents with flame arresters, four adjustable self-leveling feet, grounding connector, and trilingual warning label. Durable lead-free epoxy/polyester powder-coat finish provides excellent chemical resistance.

All cabinets are FM approved and come with a ten-year warranty.

Self-closing models also meet NFPA1 and the International Fire Code. They shut and latch automatically when a fusible link melts at 165°F (74°C) under fire conditions. Unique, concealed self-closing mechanism offers obstruction-free access to contents.

- See more at:

http://justrite.wsoldev.com/Products/Safety-Cabinets-and-Containers/Safety-Cabinets-for-Flammables/Transportable-Mini-Countertop-and-Compact-Cabinets/890200/?id=459_1157&epiworkspaceactive=true&visitorgroupsByID=#sthash.IEs2slyg.dpuf

Specifications

Model No	24168
UPC	697841123960
International Model No.	24168
Color	white
Material Specifications	Wood laminate
Dimensions, Exterior	34" W x 16.875" D
	864mm W x 429mm D
Net Weight, lbs	0.0
Net Weight, kg	0.0