

1 Gallon Plastic Outdoor Ashtray, Personal Smoker's Ceasefire®[®], Deco Black - 26806D

Product Images



Short Description

- Fire tested and FM Approved
- Galvanized steel pail
- Made of flame-retardant polyethylene
- Ideal for decks, patios and poolside areas
- ADA compliant
- Innovative self-extinguishing design

Description

Keep cigarette litter out of sight from your guests with the Personal Smoker's Ceasefire® Outdoor Ashtray in Deco Black (model 26806D). Its excellent compact design fits great on any poolside or patio.

At 30 in (762 mm) in height with an 11 in (279 mm) base diameter, this ashtray is ADA compliant and fits nicely into snug spaces and light traffic areas for smokers.

The double-drip interior design of model 26806D does an excellent job of keeping tar condensation from appearing on the exterior, something common for high humidity areas. The large head keeps rain and other unwanted litter from entering, and dissipates heat from butts. The long neck design minimizes clogging.

Its galvanized steel pail can hold up to 1 gal (4 l) of cigarette litter and has the same innovative self-extinguishing design as its larger counterpart. This outdoor ashtray is made with a flame-retardant polyethylene, fire tested and FM approved, and won't rust, dent, or crack.

Simply unscrew the lid from the base to open for maintenance, no tools are required. Optional accessories include handy disposable bucket liners made of aluminum/poly (model 26827), which can be easily twist-tied and thrown away once full.

An Anchoring Cable Kit with Padlock (model 268505) is also available, to provide extra security for your outdoor ashtray. Simply attach the 36 in (914 mm) wire rope around a railing or fence, then attach the cable end and padlock to a tie-down notch at the base.

Specifications

| | |
|-------------------------|--|
| Model No | 26806D |
| UPC | 697841095434 |
| International Model No. | 26806D |
| Color | Deco Black |
| Pallet Quantity | 32 |
| Material Specifications | Polyethylene |
| Net Weight, lbs | 4.5 |
| Net Weight, kg | 2.0 |
| Dimensions, Exterior | 30" H x 11" Outer Dia. 762mm H x 279mm Outer Dia. |
| Capacity | 1 gallon |
| Liter Capacity | 4 |
| FM Approval | Yes |