

5 Gallon Dip Tank for Cleaning Parts, Manual Cover With Fusible Link, Steel, Red - 27605

Product Images



Short Description

- Portable, safe solution to parts cleaning
- Cover stays open for convenient access
- Self-closing in case of fire

Description

Use for cleaning parts and subassemblies where the volume of work does not warrant a larger rinse tank. Portable size accommodates changing production requirements. Dip tank covers stay open for convenient access; self-closing mechanism and fusible link melts at 165°F (74°C) to snap the cover shut in case of fire.

Specifications

Model No	27605
UPC	697841010611
International Model No.	27605
Pallet Quantity	45
FM Approval	Yes
TUV Approval	Yes
Color	Red
Material Specifications	Steel
Dimensions, Exterior	13" H x 13.75" Outer Dia. 330mm H x 349mm Outer Dia.
Capacity	5 gallon
Liter Capacity	19
Net Weight, lbs	8.5
Net Weight, kg	3.9