

8 Gallon Dip Tank for Cleaning Parts, Manual Cover With Fusible Link, Steel, Red - 27608

Product Images



Short Description

- Portable, safe solution to parts cleaning
- Cover stays open for convenient access
- Self-closing in case of fire

Description

Use for cleaning parts and subassemblies where the volume of work does not warrant a larger rinse tank. Portable size accommodates changing production requirements. Dip tank covers stay open for convenient access; self-closing mechanism and fusible link melts at 165°F (74°C) to snap the cover shut in case of fire.

Specifications

Model No	27608
UPC	697841010635
International Model No.	27608
Pallet Quantity	24
FM Approval	Yes
TUV Approval	Yes
Color	Red
Material Specifications	Steel
Dimensions, Exterior	14.25" H x 15.625" Outer Dia. 362mm H x 397mm Outer Dia.
Capacity	8 gallon
Liter Capacity	30
Net Weight, lbs	11.0
Net Weight, kg	5.0