

7'W x 7'L, Ceiling Leak Diverter - 28304

Product Images



Short Description

- Redirect roof or pipe leaks to prevent water damage
- Corners contain grommets for bungee or zip tie attachment
- Constructed with cinched corners for quick and easy installation

Description

Durable, puncture resistant, and watertight EnGuard™ I PVC coated yellow fabric is designed to channel overhead pipe and ceiling leaks to containers or floor drains. Diverters help provide a fast and economical way to protect your personnel, equipment, and inventory. Simply connect to a standard garden hose to drain water safely away. Flow rate of 3.3 gal/min (12.5 L/min).

Specifications

| | |
|-------------------------|-----------------------------|
| Model No | 28304 |
| UPC | 697841156920 |
| International Model No. | 28304 |
| Color | Yellow |
| Material Specifications | PVC Coated Fabric |
| Dimensions, Exterior | 84" W x 84" L |
| | 2134mm W x 2134mm L |
| Dimensions, Folded | 18" W x 16" L x 4" H |
| | 457mm W x 406mm L x 102mm H |
| Net Weight, lbs | 7.0 |
| Net Weight, kg | 3.2 |