

## 10'W x 10'L, Ceiling Leak Diverter - 28308

### Product Images

---



### Short Description

---

- Redirect roof or pipe leaks to prevent water damage
- Corners contain grommets for bungee or zip tie attachment
- Constructed with cinched corners for quick and easy installation

## Description

---

Durable, puncture resistant, and watertight EnGuard™ I PVC coated yellow fabric is designed to channel overhead pipe and ceiling leaks to containers or floor drains. Diverters help provide a fast and economical way to protect your personnel, equipment, and inventory. Simply connect to a standard garden hose to drain water safely away. Flow rate of 3.3 gal/min (12.5 L/min).

## Specifications

---

Model No	28308
Special Price Type	Sale
UPC	697841156944
International Model No.	28308
Color	Yellow
Material Specifications	PVC Coated Fabric
Dimensions, Exterior	120" W x 120" L
	3048mm W x 3048mm L
Dimensions, Folded	18" W x 16" L x 6" H
	457mm W x 406mm L x 152mm H
Net Weight, lbs	14.0
Net Weight, kg	6.4