

12'W x 12'L, Ceiling Leak Diverter - 28312

Product Images



Short Description

- Redirect roof or pipe leaks to prevent water damage
- Corners contain grommets for bungee or zip tie attachment
- Constructed with cinched corners for quick and easy installation

Description

Durable, puncture resistant, and watertight EnGuard™ I PVC coated yellow fabric is designed to channel overhead pipe and ceiling leaks to containers or floor drains. Diverters help provide a fast and economical way to protect your personnel, equipment, and inventory. Simply connect to a standard garden hose to drain water safely away. Flow rate of 3.3 gal/min (12.5 L/min).

Specifications

Model No	28312
Special Price Type	Sale
UPC	697841156968
International Model No.	28312
Color	Yellow
Material Specifications	PVC Coated Fabric
Dimensions, Exterior	144" W x 144" L
	3658mm W x 3658mm L
Dimensions, Folded	18" W x 16" L x 6" H
	457mm W x 406mm L x 152mm H
Net Weight, lbs	20.0
Net Weight, kg	9.1