

20'W x 20'L, Ceiling Leak Diverter - 28318

Product Images



Short Description

- Redirect roof or pipe leaks to prevent water damage
- Corners contain grommets for bungee or zip tie attachment
- Constructed with cinched corners for quick and easy installation

Description

Durable, puncture resistant, and watertight EnGuard™ I PVC coated yellow fabric is designed to channel overhead pipe and ceiling leaks to containers or floor drains. Diverters help provide a fast and economical way to protect your personnel, equipment, and inventory. Simply connect to a standard garden hose to drain water safely away. Flow rate of 3.3 gal/min (12.5 L/min).

Specifications

Model No	28318
UPC	697841156999
International Model No.	28318
Color	Yellow
Material Specifications	PVC Coated Fabric
Dimensions, Exterior	240" W x 240" L
	6096mm W x 6096mm L
Dimensions, Folded	18" W x 16" L x 14" H
	457mm W x 406mm L x 356mm H
Net Weight, lbs	56.0
Net Weight, kg	25.4