


2' x 2' x 4", 10 Gallon Spill Capacity, Maintenance Spill Berm, Yellow - 28400

Product Images



Short Description

- Compact and flexible spill containment deploys instantly in the shop or field
- No assembly required—simply unfold and use
- Encased urethane foam sidewalls offer easy roll-through access without the need for a ramp
- Walls quickly spring back into place with no memory loss
- Helps comply with EPA SPCC regulations

Description

Quickly contain minor spills and leaks during temporary storage of drums, machine parts, batteries, and equipment. Lightweight EnGuard™, PVC coated fabric provides broad UV and chemical resistance. Anchor berm in place using the brass grommets in each corner. Anchor stakes not included. Order optional grates to keep products and machinery above fluid.

Helps comply with EPA for spill prevention (SPCC).

Specifications

Model No	28400
UPC	697841156722
International Model No.	28400
Color	Yellow
Material Specifications	PVC Coated Fabric
Capacity	10 gallon
Liter Capacity	38
Dimensions, Exterior	38" W 4' x H 36" L
	965mm W x 102mm H x 914mm L
Dimensions, Interior	36" W x 4" H x 36" L
	914 W x 102 H x 914 L
Dimensions, Folded	30" W x 4" H x 30" L
	762mm W x 102mm H x 762mm L
Net Weight, lbs	5.0
Net Weight, kg	2.3