

6' x 20' x 8", 598 Gallon Spill Capacity, 4-Zone Decontamination Spill Containment Berm, QuickBerm[®] - 28574

Product Images



Short Description

- Portable four-zone decon station help prevent environmental contamination
- Single-piece construction—patented inside wall-support system forms watertight wash down zones
- Quick and easy setup—no assembly required
- Durable EnGuard[™], modified PVC coated fabric withstands long-term UV exposure

Description

For emergency deployment, these multi-stage berms with patented interior walls create wash down zones that safely capture and contain contaminated solutions. Select from two-, three-, or four-zone models. Watertight, lightweight EnGuard[™], modified PVC coated fabric provides wide range of chemical resistance.

The 8-inch (203-mm) walls allow for easy entry and exit of the compartments. One ¾-in GHT drain fitting per zone. Order optional grates to keep personnel above liquid.

Specifications

Model No	28574
UPC	697841156852
International Model No.	28574
Color	Black
Material Specifications	PVC Coated Fabric
Capacity	598 gallon
Liter Capacity	2264
Dimensions, Exterior	72" W x 8" H x 240" L
	1829mm W x 203mm H x 6096mm L
Dimensions, Interior	72" W x 8"H 240" L
	1829mm W x 203mm H x 6096mm L
Dimensions, Folded	28" W x 4" H x 28" L
	711mm W x 102mm H x 711mm L
Net Weight, lbs	42.0
Net Weight, kg	19.1