

4 Drum Plastic Pallet, In-line, without Drain, EcoPolyBlend™, Yellow - 28630

Product Images



Short Description

- Keep workers safe from accidental slips indoors and avoid costly hazmat cleanup costs
- EcoPolyBlend™ high-visibility yellow is 30% recycled
- Compliance with NFPA 30, OSHA, EPA, SPCC, and fire codes
- 4 drum, in-line configuration protects against groundwater contamination from leakage and spills
- Sump capacity of 75 gal (284 L)
- Recycled content saves on oil, electricity, and landfill space

Description

The Justrite EcoPolyBlend™ Spill Control Pallet (4 drum, yellow — model 28630) keeps accidental spills under control, resisting unwanted chemical exposure from hazardous acids, caustics, and solvents. They are ideal for storing 30 gal or 55 gal drums.

This in-line 4 drum, high-visibility yellow model measures 97 in W x 9 in H x 25 in D (2464 mm W x 229 mm H x 635 mm D) and is made from 30% recycled polyethylene. It has an oversized sump able to hold the contents of a 55 gal (200 L) drum in the event of a leak or rupture—meeting or exceeding the most stringent spill containment regulations. Our customers trust the reliability of our spill control pallets to ensure that unwanted spills do not impede or otherwise impact daily operations.

EcoPolyBlend structured spill containment pallets ensure seamless, robust construction that eliminates leaks and features removable self-locating grates that lift off for quick clean up. At nearly 2.5 in (64 mm) thick, the UV-protected polyethylene offers superior crack resistance and is able to stand up to the harshest chemicals. Choose from square or in-line configurations, both of which are NFPA 30, OSHA, EPA, SPCC, and fire code compliant.

With a net weight of 77 lb (34.9 kg) and uniform distributed load-bearing capacity of 5000 lb (2268 kg) from -30°F to 120°F (-39°C to 49°C), Justrite spill control pallets are the safest and most efficient way to store drums inside or outside, any time of year. They are also easy to utilize, with forklift pockets for easy relocation and in-line design that is ideal when space is limited.

Why do you need it?

Spills happen, even in the most safety-conscious and well-managed workplaces. When these occur, it is essential to capture leaks from chemical drums immediately so that hazardous materials never reach the environment.

Spill containment pallets are the main base for catching spills. They can be used alongside other containment measures (such as trays or accumulation centers), but these rigid pallets are the bedrock for any spill containment system.

Environmentally-friendly EcoPolyBlend spill control pallets provide the perfect solution to containing drum leaks and spills. They keep small incidents from escalating into something more serious. These pallets can also be used as a battery holding center to capture incidental leaks, and as a workstation for waste collection or satellite accumulation centers.

In addition, EcoPolyBlend pallets are made from post-industrial resin, which means they repurpose waste to be used in the waste collection process and promote sustainability on both ends. This two-pronged recycling approach is beneficial for the natural environment, as well as your work environment.

Specifications

Model No	28630
UPC	697841132566
International Model No.	28630
Color	Yellow
Material Specifications	Recycled Polyethylene
UL Environmental Approval	Yes
Complies with NFPA Code 30	Yes
OSHA Compliance	Yes
EPA Compliance	Yes
SPCC Compliance	Yes
Percent Recycled	30
Sump Capacity - Gallons	75
Sump Capacity - liters	284
Load Bearing Capacity, lbs	5000
Load Bearing Capacity, kg	2268
Dimensions, Exterior	97" W x 9" H x 25" D
	2464mm W x 229mm H x 635mm D
Net Weight, lbs	77.0
Net Weight, kg	34.9