

Spill Containment Indoor/Outdoor Drum Caddy, Fits 55 Gallon Drums, Polyethylene, Yellow - 28664

Product Images



Short Description

- Convenient drum handling and dispensing with built-in spill containment
- Compliance with NFPA 30, OSHA, EPA, SPCC, and fire codes
- Portable, ergonomic design
- Sump capacity of 66 gal (250 L)

Description

The Justrite EcoPolyBlend™ Spill Containment Indoor/Outdoor Caddy (model 28664) is a portable unit with wheels that allows one person to easily transport a full 55-gal (200-L) drum.

The ergonomically designed caddy measures 32 in W x 26 in H x 72 in D (813 mm W x 660 mm H x 1829 mm D), with two tension straps to hold drums securely in place. A 66 gal (250 L) spill sump contains chemical spills, eliminating hazards and hassles. The exclusive open-view sump design makes cleanup simple and quick, and the durable yellow polyethylene construction provides maximum corrosion resistance and leakproof protection.

With a net weight of 120.0 lb (54.4 kg) and a safe allowable uniform distributed load of 1250 lb (567 kg) based on a service temperature range of -30°F to 120°F (-39°C to 49°C), this caddy is extremely sturdy. It is EPA, SPCC, NFPA 30, OSHA, EPA, and SPCC compliant and meets fire codes.

Why do you need it??

Drums need to be moved — and they should be moved in the safest and easiest manner. Using a caddy not only allows for convenient, ergonomic movement with ease, but it easily accommodates a full leak from a 55 gal drum, with simple cleanup from the open-view sump.

This is more than just a hand truck for drums or barrels. Model 28664 serves as a specialized apparatus that makes it easy to move drums on and off spill pallets. Using a caddy improves safety for employees and others, by minimizing injuries and negating unnecessary spills.

Specifications

Model No	28664
UPC	697841134508
International Model No.	28664
Color	Yellow
Material Specifications	Polyethylene
UL Environmental Approval	Yes
Complies with NFPA Code 30	Yes
OSHA Compliance	Yes
EPA Compliance	Yes
SPCC Compliance	Yes
Sump Capacity - Gallons	66
Sump Capacity - liters	250
Load Bearing Capacity, lbs	1250
Load Bearing Capacity, kg	567
Dimensions, Exterior	32" W x 26" H x 72" D
	813mm W x 660mm H x 1829mm D
Net Weight, lbs	120.0
Net Weight, kg	54.4