

Stack Module for Drum Management System, Forklift Channels, EcoPolyBlend™, Black - 28669

Product Images



Short Description

- Holds two additional drums to double the drum management system capacity
- EcoPolyBlend™ is 100% recycled black polyethylene

- Complies with EPA SPCC regulations and meets fire codes

Description

The Stack Module holds two additional drums to double the system capacity for a load of 1500 lb (680 kg). When storing both 30- and 55-gallon (110- and 200-L) drums, the smaller drums should be placed on the top of the stack module.

The Drum Management System is a space-saving, stackable design that stores up to four 30- and/or 55-gallon (110- and/or 200-L) drums of Class 1B or 1C flammables and combustibles or nonhazardous liquids. 100% molded polyethylene construction provides maximum chemical resistance—preventing corrosion, deterioration and leaks. Molded-in drum lock-channels hold drums in place. The system consists of three parts: a base module, stack module and dispensing shelf — EACH PIECE SOLD SEPARATELY

To be used in conjunction with:

The Base Module holds two drums with a 3060-lb (1388-kg) total load capacity. Easily relocate the base module with a forklift when empty. The 66-gallon (250-L) open-view containment sump makes it easy to spot any spills for a quick cleanup.

The Dispensing Shelf has a load capacity of 60 lb (27 kg), and mounts securely to the stack module for convenient dispensing from the upper level.

EPA, SPCC compliant and meets fire codes.

Load Bearing Capacity — (UDL) Uniformly distributed Load - 1250lbs. (567 kgs) per drum.

Base module capacity of 3060 Lbs. includes stack module and shelf

Note: When storing different sized drums, always place two smaller drums on top of two larger drums.

Safe allowable uniform distributed load of 1500 lbs (680 kg) based on a service temperature range of -30°F to 120°F (-39°C to 49°C)

Specifications

Model No	28669
UPC	697841134553
International Model No.	28669
Color	Black
Material Specifications	Recycled Polyethylene
UL Environmental Approval	Yes
Percent Recycled	100
Load Bearing Capacity, lbs	1500
Load Bearing Capacity, kg	680
Dimensions, Exterior	12" H x 49" W x 46" D x 46" L
	305mm H x 1245mm W x 1168mm D x 1168mm L
Net Weight, lbs	70.0
Net Weight, kg	31.8