

# IBC Indoor Pallet, with Forklift Pockets, EcoPolyBlend™, Black - 28674

## Product Images



## Short Description

- Reliable spill protection and safe storage for indoor IBCs
- Complies with EPA SPCC regulations and meets fire codes
- Ships fully assembled

## Description

Constructed of durable 40% recycled polyethylene, these intermediate bulk container pallets offer excellent chemical resistance. Accepts IBCs up to 48"W x 48"D x 53"H (1219 mm x 1219 mm x 1346 mm). Large leakproof sump exceeds regulations and protects against high volume spills. Sturdy pillar supports accept up to 9000 lb (4082 kg) uniformly distributed load. Removable pillars make for easy sump cleanup. Pallet

features forklift pockets for relocation when empty. Ships fully assembled.

EPA, SPCC compliant and meets fire codes.

(UDL) Uniformly Distributed Load - 1250 Lbs/567 Kgs. per drum, for DrumSheds™ and Pallets

Safe allowable uniform distributed load of 9000 lbs (4082 kg) based on a service temperature range of -30°F to 120°F (-39°C to 49°C)

## Specifications

---

Model No	28674
UPC	697841133563
International Model No.	28674
Pallet Quantity	2
Color	Black
Material Specifications	Recycled Polyethylene
UL Approval	Yes
UL Environmental Approval	Yes
OSHA Compliance	Yes
EPA Compliance	Yes
SPCC Compliance	Yes
Percent Recycled	40
Sump Capacity - Gallons	372
Sump Capacity - liters	1408
Load Bearing Capacity, lbs	9000
Load Bearing Capacity, kg	4082
Dimensions, Exterior	37.5" H x 55" W x 55" D
	953mm H x 1397mm W x 1397mm D
Net Weight, lbs	339.4
Net Weight, kg	154.0