

Rolling Cart for 30 Gallon and Piggyback Safety Cabinets, Poly Caster Wheels - 84001

Product Images



Short Description

Key Benefits

- Convert your cabinets into mobile workstations
- 30 gallon and Piggyback style cabinets

Description

Rolling Cart makes it easy to move a heavy safety cabinet—transport solvents and chemicals directly to your work area. All welded 1/8" (3-mm) thick heavy-duty steel with reinforced corners provides superior durability. Large 5" (127-mm) poly caster wheels feature brakes for added safety. Ergonomic 1-1/4" (31.75-mm) push handle is removable. Frame fits any cabinet with footprint of 43"W x 18"D (1092 mm x 457 mm) with a maximum height of 44" (1118 mm).

Specifications

Model No	84001
UPC	697841124028
International Model No.	84001
Color	Black
Material Specifications	Steel
Dimensions, Exterior	42" H x 43.25" W x 18.25" D
	1067mm H x 1099mm W x 464mm D
Net Weight, lbs	45.0
Net Weight, kg	20.4