

Double Cylinder Hand Truck, 10.5" Pneumatic Wheels - 35028

Product Images



Short Description

- Configured with 10.5-in (267-mm) steel hub pneumatic wheels with dual ball bearings for easier rolling—less effort required
- Rated at 700-lb (318-kg) weight capacity
- Accepts two gas cylinders with combined diameters up to 23-in (584-mm), including fuel and oxidizer cylinders common in welding applications

Description

Never compromise safety when it comes to handling heavy compressed gas cylinders. Constructed of 1-in (25-mm) and 1.25-in (32-mm) diameter round steel tube with continuous welding, these durable, double-cylinder trucks provide optimum safety, strength, and longevity. Floor plate made of thick 11-gauge (3-mm)

steel with safety fins prevents warping or breaking. The unique zero-lift height loading floor plate lays flat, thereby eliminating the need to lift cylinder during loading and unloading. Corrosion-resistant powder coat finish throughout for long life and smooth handling.

Hold gas cylinders in place independently for improved safety. Heavy-duty 1.5- x 54-in (38-mm x 1372-mm) polypropylene support straps, lab tested to 1138-lb (516-kg), feature steel cinch buckles for secure attachment of cylinder—eliminate any cylinder rolling potential seen in chain-secured units. Exclusive bumper guard edging grips cylinder and minimizes damage to cylinder and hand truck.

Optional locking posts and collar plate system model 35084 ensures total cylinder immobilization, or accessorize hand trucks with a tool tray or lockable tool box for securing torches and other equipment—models 35388 and 35386 respectively.

Helps comply with OSHA, NFP1, NFPA 55, and CGA.

Specifications

Model No	35028
UPC	697841209695
Cylinder Capacity	2
Minimum Cylinder Diam (in)	5
Cylinder Capacity with Max Cylinder Dia	(1) 10 inch and (1) 13 inch
Main Wheel Type	Pneumatic
Main Wheel Size (inch)	10.5
Main Wheel Size (mm)	267
Weight Capacity (lb)	700
Weight Capacity (kg)	318
Strap Style	Poly Cinch Strap with Steel Buckle
Straps Per Cylinder	1
Material Specifications	Steel
Complies with NFPA 1 Fire-Code	Yes
NFPA 55	Yes
OSHA Compliance	Yes
CGA	Yes
Net Weight, lbs	50
Net Weight, kg	23
Net Dimensions (W x D x H)	33 x 19 x 47 inches
	838 x 483 x 1194 mm