

Gas Cylinder Cart, 4 Cylinder Capacity - 35056

Product Images



Short Description

- Carts include two 4-in (102-mm) locking swivel casters and two fixed direction casters for movement of cylinders with ease
- Exclusive bumper guard edging with steel reinforced vinyl protects your cylinders from damage while providing extra grip
- Heavy-duty 1.5- x 54-in (38-mm x 1372-mm) polypropylene support straps, rated at 1138-lb (516-kg), feature steel cinch buckle and hold individual cylinders securely to prevent tipping

Description

Designed for the safe transport of industrial and commercial use compressed gas cylinders, these storage carts store cylinders from 4- to 12-in (102- to 305-mm) in diameter back-to-back. Constructed from 7- and 11-gauge (5- and 3-mm) steel, each unit includes upper and lower brackets to provide added support and securement locations for cylinders. Offset deck design, reinforced with three sets of support bars for strength

and rigidity, makes cylinder loading easy and safe at only 1.75-in (45-mm) off the ground. Powder-coated steel parts ensure long service life and chemical resistance.

For an improved level of safety on any installation, mobile stands include openings to retrofit secondary support chains, one for each strap. Order model 35366 to get optional chain(s).

Helps comply with OSHA, NFP1, NFPA 55, and CGA.

Specifications

Model No	35056
UPC	697841210110
Cylinder Capacity	4
Minimum Cylinder Diam (in)	4
Cylinder Capacity with Max Cylinder Dia	(1) 12 inch
Main Wheel Type	Swivel Caster
Main Wheel Size (inch)	4
Main Wheel Size (mm)	102
Weight Capacity (lb)	1600
Weight Capacity (kg)	726
Strap Style	Poly Cinch Strap with Steel Buckle
Straps Per Cylinder	2
Material Specifications	Steel
Complies with NFPA 1 Fire-Code	Yes
NFPA 55	Yes
OSHA Compliance	Yes
CGA	Yes
Net Weight, lbs	133
Net Weight, kg	60
Net Dimensions (W x D x H)	24 x 40 x 31 inches
	610 x 1016 x 787 mm