

Spigot for Carboys, Easy-Grip, Up/Down, Package of Two - 12900

Product Images



Short Description

- Leakproof, controlled fluid transfer
- Easy-grip lever controlling two flow rates—continuous or manual
- Designed to withstand 26-gallons (100-liters) of pressure

Description

- Easy-grip lever controlling two flow rates—continuous or manual
- Designed to withstand 26-gallons (100-liters) of pressure

Designed with 1-1/8-inch internal threads and a hard stop to prevent over tightening and seal damage, these leakproof polypropylene spigots feature 5/8- and 3/4-inch hose barbs, and a standard internal luer taper to fit a male barb adapter. Large lever controls two flow rates, one for continuous, locked flow and the other for a faster, manual flow. Spigots can be autoclaved at 15 PSI and 250°F (121°C) for 20 minutes.

Specifications

Model No	12900
UPC	697841182387
International Model No.	12900
Material Specifications	Polypropylene
Dimensions, Exterior	4" H x 1.5" W x 2.9" L 102mm H x 38mm W x 74mm L
Net Weight, lbs	0.2
Net Weight, kg	0.1