

Steel Gas Cylinder Stand, 4 Cylinder Capacity, Back-to-Back - 35296

Product Images



Short Description

- Fully welded construction using 11-gauge (3-mm) steel provides structural integrity and longevity
- Exclusive bumper guard edging with steel reinforced vinyl protects your cylinders from damage while providing extra grip
- Accepts cylinders from 4- to 12-in (102- to 305-mm) in diameter
- Back-to-back cylinder storage for maximum space utilization

Description

Designed for the safe storage of industrial and commercial use compressed gas cylinders, these storage stands help prevent dangerous tipping situations. Powder-coated to ensure long service life and chemical resistance. Pre-drilled holes in base for floor mounting with application specific fasteners (not included).

Two heavy-duty polypropylene support straps, 1.5- x 54-in (38-mm x 1372-mm) and rated at 1138-lb (516-kg), feature steel cinch buckle and hold individual cylinders securely against integral bracket. For an improved level of safety for any installation, all brackets include openings to retrofit secondary support chains, one set for each cylinder strap location.

Helps comply with OSHA, NFP1, NFPA 55, and CGA.

Specifications

Model No	35296
UPC	697841211032
Cylinder Capacity	4
Minimum Cylinder Diam (in)	4
Cylinder Capacity with Max Cylinder Dia	(4) 12 inch
Mount Type	Floor
Mount Holes	4
Mount Hole Size (inch)	0.406
Strap Style	Poly Cinch Strap with Steel Buckle
Straps Per Cylinder	2
Material Specifications	Steel
Complies with NFPA 1 Fire-Code	Yes
NFPA 55	Yes
OSHA Compliance	Yes
CGA	Yes
Net Weight, lbs	69
Net Weight, kg	31
Net Dimensions (W x D x H)	32 x 23 x 30 inches
	813 x 584 x 762 mm