

Steel Medical Oxygen Cylinder Stand, One 3.25 to 4.25" Diameter Cylinder Capacity - 35326

Product Images



Short Description

- One Cylinder Capacity
- Corrosion-resistant coating
- Pre-drilled Mounting holes

Description

Commonly used for medical oxygen or calibration gases in laboratories, this ring stand uses 0.375-in (10-mm) nylon set screws to hold cylinders from 3.25- to 4.25-in (83- to 108-mm) in place. Constructed using steel with corrosion-resistant powder coating, the stands include mounting holes for permanent installations.

Helps comply with OSHA, NFP1, NFPA 55, and CGA.

Specifications

Model No	35326
UPC	697841211186
Cylinder Capacity	1
Minimum Cylinder Diam (in)	3.25
Cylinder Capacity with Max Cylinder Dia	(1) 4.25 inch
Mount Type	Bench
Mount Holes	3
Mount Hole Size (inch)	0.312
Material Specifications	Steel
Net Weight, lbs	4
Net Weight, kg	2
Net Dimensions (W x D x H)	9.5 x 9.5 x 7 inches
	241 x 241 x 178 mm