

## Medical Oxygen Cylinder Stand, One 7.75 to 8.75" Diameter Cylinder Capacity - 35330

### Product Images

---



### Short Description

---

- One cylinder capacity
- Corrosion-resistant coating
- Pre-drilled mounting holes

## Description

---

Commonly used for medical oxygen or calibration gases in laboratories, this ring stand uses 0.375-in (10-mm) nylon set screws to hold cylinders from 7.75- to 8.75-in (197- to 222-mm) in place. Constructed using steel with corrosion-resistant powder coating, the stands include mounting holes for permanent installations.

Helps comply with OSHA, NFP1, NFPA 55, and CGA.

## Specifications

---

|   |                        |
|---|------------------------|
| Model No                                | 35330                  |
| UPC                                     | 697841211209           |
| Cylinder Capacity                       | 1                      |
| Minimum Cylinder Diam (in)              | 7.75                   |
| Cylinder Capacity with Max Cylinder Dia | (1) 8.75 inch          |
| Mount Type                              | Bench                  |
| Mount Holes                             | 4                      |
| Mount Hole Size (inch)                  | 0.312                  |
| Material Specifications                 | Steel                  |
| Net Weight, lbs                         | 8                      |
| Net Weight, kg                          | 4                      |
| Net Dimensions (W x D x H)              | 16.5 x 16.5 x 7 inches |
|   | 419 x 419 x 178 mm     |