



# 30 Gallon, Portable Hughes Self-Contained Safety Shower with Eye/Face Wash, Mobile - 40K45G

## Product Images



## Short Description

# HUGHES



## Justrite Safety Group

- Mobile eye/face wash and shower provides a continuous flow of water for 1-1/2 minutes
- High-performance quarter-turn ball valves made of 316L stainless steel endure the harshest environments and site conditions
- Covered, durable acrylic-capped ABS eye/face wash protects the bowl and eyewash diffusers from dust and debris
- Twin diffusers provide a gentle flow of aerated water and prevent further injury to the eyes

## Description

---

This highly mobile, self-contained safety shower with eye/face wash holds 30-gallons (114-liter) of water for use in responding to potential accidents anywhere. Suitable for temporary use, this exclusive design features a corrosion-resistant, polypropylene-lined pressurized cylinder and only requires the connection of a hose from a water main to fill it ready for use.

Easily maneuvered by one person, it incorporates a stainless steel frame and large diameter pneumatic tires—adjustable wheel spacing allows the unit to go through standard door openings. Disconnect shower arm for compact transportation.

The eye/face wash with high, ANSI-compliant flow rate features an integral lid connected to the water valve for automatic operation—activate by simply pulling down the lid. Easy-to-reach flow regulator valve positioned on the side of the bowl adjusts to suit the severity of the accident. Suitable for Class 1 Division 2 hazardous areas, as well as non-hazardous areas.

## Specifications

---

Model No	40K45G
Color	White
UPC	805042001738
Capacity	30 gallon
Net Weight, lbs	176
Net Weight, kg	80
Dimensions, Exterior	91" H x 29" W x 57.5" D 2315mm H x 734mm W x 1462mm D
Water Inlet Size NPT	1/2 in quick release hose connector
Minimum Operating Pressure	3 bar g, 43 PSI
Maximum Operating Pressure	5.5 bar g, 79 PSI
Water Flow Shower/Body Liters/min	75.7
Water Flow Shower/Body US Gal/min	20
Water Flow Eye/Face Liters/min	12
Water Flow Eye/Face US Gal/min	3
Operating Valve Material	Stainless steel, full bore, stay open ball valve
Eye/Face Wash Bowl Material	Acrylic-Capped ABS Plastic
Mounting Type	Portable
Pipework Material	Stainless Steel
Activation Method	Shower: Push down lever, Eye/Face: Pull lid down
Minimum Ambient Temperature, °F	41
Minimum Ambient Temperature, °C	5
Maximum Ambient Temperature, °F	95
Maximum Ambient Temperature, °C	35
Operation Duration, min	1.5

## Prop 65

---

**⚠️WARNING:** This product can expose you to chemicals including lead, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to [www.P65Warnings.ca.gov](http://www.P65Warnings.ca.gov).