




4 Gallon, 1 Shelf, 1 Door, Manual Close, Flammable Cabinet, Sure-Grip® EX Countertop, Red - 890401

Product Images





Short Description

- Ideal for the safe storage of solvents and flammable liquids on countertops
- Exterior dimensions of 22 in H x 17 in W x 17 in D (559 mm H x 432 mm W x 432 mm D)
- Storage capacity of 4 gal (15 L) of flammable liquids
- Portable size for use on workbenches and other limited spaces for access to often-used chemicals
- Fire-resistant, leak-tested design
- Complies with OSHA, NFPA 30 and NFPA 1

Description

The Justrite Sure-Grip® EX Countertop Safety Cabinet with a Manual Close Door (model 890401) is for the safe and code-compliant storage of solvents and flammable liquids, such as aerosols, cleaners, and degreasers, on countertops and workbenches. Designed to increase accessibility without compromising safety, this red cabinet is ideal for maintenance garages with limited floor space.

It is available in a portable size with exterior dimensions of 22 in H x 17 in W x 17 in D (559 mm H x 432 mm W x 432 mm D). Model 890401 can store 4 gal (15 L) of flammable liquids. It easily sits on countertops and is also wall-mountable with an optional wall hanger.

This model is constructed with a sturdy 18-gauge (1-mm) thick steel double-wall, with 1.5 in (38 mm) of insulating air space for fire resistance. The fully welded, not riveted, construction holds the squareness of the unit for a longer life and offers greater protection in a fire since air gaps are reduced.

The high-performance, manual-close, self-latching door (fail safe, 3-point stainless steel) opens to a full 180 degrees and closes securely for maximum protection under fire conditions when pushed shut. Continuous piano hinges ensure the door closes smoothly every time.

For added security, each cabinet comes with an innovative U-Loc™ handle that does not require manual rotation to engage the mandatory latch. Cabinets include a cylinder lock and key set, or you can choose to use your own padlock. Haz-Alert™ reflective warning labels that read “FLAMMABLE – KEEP FIRE AWAY” are highly visible under fire conditions or during power outages when illuminated with a flashlight.

Model 890401 features one patented, galvanized steel SpillSlope® shelf designed to direct spills to the back and bottom into a 2-in (51-mm) leak-tested sump that meets EPA requirements. Adjustable on 3-in (76-mm) centers, all SpillSlope shelves meet ANSI MH28.1 standards with a 350-lb (159-kg) safe allowable load. Welded shelf hangers interlock with the shelf to offer maximum stability with no flimsy brackets to lose. For replacement shelves, use model 29935.

The cabinet also features dual vents with flame arresters, four adjustable self-leveling feet, and a built-in grounding connector. Its durable lead-free epoxy/polyester powder-coat finish provides excellent chemical resistance inside and out, as well as minimizes the effects of corrosion and humidity.

Justrite supplies more than 300 safety cabinet models ranging from 4- to 115-gal (15- to 435-L), to meet a versatile range of safety, compliance, and storage requirements.

All Justrite cabinets carry a 10-year warranty. Model 890401 complies with OSHA, NFPA 30, and NFPA 1 requirements.

Safety Considerations for Countertop Cabinets

The requirements for handling and storing chemicals are complex and depend on how flammable the liquid is. There is no room for error, so it is critical to choose a safety cabinet that has been independently tested to meet the standards of your industry and local jurisdictions. Not just any safety cabinet will do. Justrite flammable cabinets are best in class and are trusted within a wide range of industrial settings across the world, including laboratories, manufacturing, oil refineries, chemical processing plants, and more.

For more information, please consult our workplace safety article about the [requirements for flammable liquid storage](#).

Specifications

Model No	890401
UPC	697841112049
International Model No.	8904011
Color	Red
Material Specifications	18-Gauge Steel
OSHA Compliance	Yes
Complies with NFPA Code 30	Yes
Capacity	4 gallon
Liter Capacity	15
Number of Doors	1
Door Type	Manual
Number of Shelves	1
Adjustable Shelves	Yes
Dimensions, Exterior	22" H x 17" W x 17" D
	559mm H x 432mm W x 432mm D
Dimensions, Interior	18.5" H x 13.8" W x 13.8" D
	470mm H x 349mm W x 349mm D
Height (Inches)	22
Width (Inches)	17
Depth	17
Net Weight, lbs	56.0
Net Weight, kg	25.4