



22 Gallon, 1 Shelf, 2 Doors, Manual Close, Corrosives/Acid Safety Cabinet, Sure-Grip® EX Under Counter, Blue - 892302

Product Images





Short Description

- Take advantage of unused undercounter space
- Offer same quality safety features as cabinets for flammables
- FM-approved
- Ten-year warranty

Description

Research environments using many different types of chemicals have special storage requirements. Whether using acids, bases or solvents, it is critical that incompatible liquids are segregated to avoid disastrous explosions or fire. The SDS (Safety Data Sheet) should be reviewed to determine chemical characteristics and recommended storage practices.

Safely store corrosives under a workbench or lab counter for quick and easy access with these Justrite blue steel Undercounter safety cabinets for corrosives, which have the same quality safety features as the cabinets for flammables. All models come with double-wall construction, dual vents, grounding wire connections, adjustable shelves, leakproof sills, three-point self-latching doors and leveling feet. Manual-close door(s) opens to a full 180 degrees and self-latches when pushed closed.

Additionally, they include polyethylene trays attached to galvanized steel shelves and a separate polyethylene liner for the bottom sump resist aggressive chemicals. Easily remove the liner for quick cleaning of drips and leaks. An all epoxy baked-on powder-coat finish, inside and out, provides increased chemical resistance.

Manual close models meet OSHA and NFPA 30. Cabinets are FM approved and come with a ten-year warranty.

Specifications

Model No	892302
UPC	697841113114
International Model No.	8923021
Color	Blue
Pallet Quantity	2
Material Specifications	18-Gauge Steel
FM Approval	Yes
OSHA Compliance	Yes
Complies with NFPA Code 30	Yes
Capacity	22 gallon
Liter Capacity	83
Number of Doors	2
Door Type	Manual
Number of Shelves	1
Adjustable Shelves	Yes
Dimensions, Exterior	35" H x 35" W x 22" D
	889mm H x 889mm W x 559mm D
Dimensions, Interior	27.4" H x 31.8" W x 18.8" D
	695mm H x 806mm W x 476mm D
Height (Inches)	35
Width (Inches)	35
Depth	22
Net Weight, lbs	154.0
Net Weight, kg	69.9