




30 Gallon, 2 Door, Manual Close, 6 Can, Safety Cabinet with Cans Combo, Sure-Grip®, Yellow - 8930008

Product Images





Short Description

- Cabinet and can value package
- Available in 30-gallon (114L) cabinets with six cans or 45-gallon (170L) cabinets with nine cans
- Manual or self-closing doors

Description

Yellow flammables cabinets with U•Loc™ padlockable paddle handle, Haz-Alert™ labeling and SpillSlope™ shelves are combined with our popular 5-gallon, Type I safety cans for an unbeatable value. Value packages are available in 30-gallon (114L) cabinets with six cans, or 45-gallon (170L) cabinets with nine cans.

Specifications

Model No	8930008
UPC	697841120891
International Model No.	8930008
Color	Yellow
Material Specifications	18-Gauge Steel
FM Approval	Yes
OSHA Compliance	Yes
Complies with NFPA Code 30	Yes
Capacity	30 gallon
Liter Capacity	114
Number of Doors	2
Door Type	Manual
Number of Shelves	1
Adjustable Shelves	Yes
Dimensions, Exterior	44" H x 43" W x 18" D
	1118mm H x 1092mm W x 457mm D
Dimensions, Interior	39.6" H x 39.5" W x 14.6" D
	1006mm H x 1003mm W x 370mm D
Height (Inches)	44
Width (Inches)	43
Depth	18
Net Weight, lbs	238.0
Net Weight, kg	108.0