

# 2-Drum, 2-Hour Fire-Rated Outdoor Safety Locker - 912020

## Product Images



## Short Description

---

- 2-hour fire-rated construction for safe and secure storage of flammables and combustibles
- 90-minute fire rated door
- Meets EPA, NFPA 30 and NFPA 1 requirements; FM-approved
- Customizable with a variety of optional features and accessories

## Description

---

Standard features include:

- 2-hour fire-rated construction — backed by a 15-year structural warranty
- 90-minute fire-rated door — third party tested and labeled
- Gravity air flow vents — UL Listed fire dampers with fusible links
- Secondary containment — leakproof all welded sump
- Removable, galvanized steel grate flooring
- 42-inch (1.07-m) wide door with UL Listed, keyed lockset for security
- Door closer — ensures doors close automatically
- NFPA 704 diamond decal provides "Right to Know" information
- Multiple static grounding connections
- Anchoring plates for maximum hold down protection
- Chemical and UV resistant coating, inside and out
- Forklift channels for easy relocation
- Meets EPA, NFPA 30 and NFPA 1 requirements
- FM-approved — including third party tested, fire-rated wall and roof design

Customize the locker to meet specific applications with a variety of [optional features and accessories](#), including loading ramp, shelving, grounding kit, fire protection, heating/cooling, insulation, and lighting packages.

NOTE: Exterior dimensions include anchoring plates and door hardware.

## Specifications

---

Model No	912020
UPC	697841158597
International Model No.	912020
Color	Bone
Material Specifications	Steel
FM Approval	Yes
UL Approval	Doors
Complies with NFPA Code 30	Yes
Complies with NFPA 1 Fire-Code	Yes
EPA Compliance	Yes
Dimensions, Exterior	77.5" H x 71" W x 42" D 1969mm H x 1803mm W x 1676mm D
Dimensions, Interior	54" H x 53.5" W x 29.5" D 1372mm H x 1359mm W x 749mm D
55-Gallon Drum Capacity	2
Base Capacity, lbs	2000
Base Capacity, kg	907.2
Number of Doors	1
Door Type	Fire-rated
Door Hinge	Left
Door Height inch	51
Door Width inch	42
Door Height mm	1295
Door Width mm	1067
Sump Capacity - Gallons	88
Sump Capacity - liters	333

Sump Depth - inch	13.5
Sump Depth - mm	343
Storage Capacity cubic feet (Int Volume)	49
Storage Capacity cubic meters (Int Volume)	1.4
Net Weight, lbs	1584.0
Net Weight, kg	718.5