


Covered ABS Eye and Face Wash, Hughes Emergency Cubicle Shower - SD32K45G

Product Images



Short Description

HUGHES



Justrite Safety Group

- Integral drain sump and strip screens reduce the risk of surplus contaminated water outside of the cubicle area
- ANSI compliant eye/face wash with acrylic capped ABS lid protects against dust and debris

Description

Designed for locations where space is at a premium or the emergency safety shower needs to be enclosed, this all-in-one ANSI-compliant combination cubicle shower and eye/face wash helps prevent overspray and is activated by hand upon entry. The cubicle shower has a stainless steel hollow section frame enclosed in GRP sheeting with stainless steel pipes for corrosion resistance and extended life. The exterior sheeting includes universal pictogram signs and green and white safety stripes.

Mounted on the inside of the cubicle for maximum benefit, the eye/face wash with high, ANSI-compliant flow rate includes aerated diffusers with fine mesh strainers and an individual flow controller which provide a soft, scrubbing action to the eyes and face. Covered bowl also ensures that the eyewash nozzles and bowl remain clean and free from contamination at all times—no dust covers needed. Activate by simply pulling down the cover. Easy-to-reach flow regulator valve positioned on side of bowl adjusts to suit the severity of the accident.

The system features a specially designed, high-performance quarter-turn ball valve made of 316L stainless steel to endure the harshest environments and site conditions. Low operating torque to open valve offers reliable, easy on/off operation when emergencies occur. Valve includes an integral, heavy-duty stainless steel stop-plate to handle rough operation without failure. Includes an inspection record tag for recording test and service history.

Specifications

Model No	SD32K45G
Color	White
UPC	805042000793
Net Weight, lbs	255
Net Weight, kg	116
Dimensions, Exterior	94.8" H x 40.2" W x 41.3" D
	2408mm H x 1021mm W x 1021mm D
Water Inlet Size NPT	1 in (M)
Minimum Operating Pressure	2 bar g, 29 PSI
Maximum Operating Pressure	6 bar g, 87 PSI
Water Flow Shower/Body Liters/min	76
Water Flow Shower/Body US Gal/min	20
Water Flow Eye/Face Liters/min	11.4
Water Flow Eye/Face US Gal/min	3
Operating Valve Material	Shower: 316L Stainless, Eyewash: Chrome plated brass
Eye/Face Wash Bowl Material	Acrylic-Capped ABS Plastic
Mounting Type	Floor
Pipework Material	Stainless Steel
Activation Method	Shower: Pull Lever, Eye/Face wash: Pull Lid Forward
Eye/Face Wash Bowl Interior Dimensions	9.5" W x 8" D
	241mm W x 203mm D
Rose Diameter, inches	10
Rose Diameter, mm	254
Minimum Ambient Temperature, °F	41
Minimum Ambient Temperature, °C	5
Maximum Ambient Temperature, °F	95

Maximum Ambient Temperature, °C

35

Prop 65

 **WARNING:** This product can expose you to chemicals including lead, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov.