

KERN 317-14

Individual weight, OIML Class E2, 10 kg, Button, stainless steel polished (OIML)



Article codes, product groups & Status information

Model article-code	317-14
Model-Serie	317
Assortment	KERN
Segment	Prüfgewichte
ProductGroup	OIML E2 Prüfgewichte
PM Status	Aktiv
Product usage type	Hauptartikel;Zubehör/DL
EAN code (Model)	4045761003767
SuccessorModel	317-14-2022i; 317-14-2022a
Planned start date	2004-1HJ

Technical data - Primary

Nominal value	10 kg
Tolerance (OIML)	16 mg
Case aluminium	317-140-600
Case plastic	317-140-400
Case wood	317-140-100

Technical data - Construction

Material	Edelstahl poliert (OIML)
----------	--------------------------

Technical data - Measuring system

NominalValue3	10 kg
OIML class	E2
OIML conform	Yes

Functions

ToleranceOIML3	16 mg
Density (kg/m ³)	7950
Volume (cm ³)	1250

Technical data - Packing & Shipping

Dimensions packaging (WxDxH)	100x100x185 mm
Gross weight	10 kg
Net weight	10 kg
Shipping method	Paketdienst
Packaging component - by weight - plastics	0 g
Delivery time	1 d

Technical data - Verification

Verification possible	Yes
-----------------------	-----

Price & Commercials

List price	990.00 €
Warranty	36 mon

Optional Services

DAkKS Calibration	962-344
-------------------	---------

KERN 317-14

Individual weight, OIML Class E2, 10 kg, Button, stainless steel polished (OIML)



Standard

