

# KERN 328-01

**KERN**

Milligram weights, F1, 1 mg, Platelet, stainless steel polished



Category	
Brand	KERN
Product category	Individual weight
Product group	OIML F1
Product family	328

Measuring System	
Test weight - volume (cm <sup>3</sup> )	0,0004
Conformity assessment possible	✓
Test weight - Density uncertainty (kg/m <sup>3</sup> )	170
Test weight - volume uncertainty (cm <sup>3</sup> )	0,0001
Weight OIML class	F1
Test weight - nominal value	1 mg
Permissible tolerance according to OIML (+/-)	0,02 mg
Test weight - Density (kg/m <sup>3</sup> )	7960
OIML-compliant	✓

Construction	
Shape weight	Platelet
Dimensions weight (W×D×H)	3,5×3,5×3 mm
Material	stainless steel polished
Adjustment method	Filing

Services (optional)	
Article number for DAkkS calibration	962-451
Article number for guaranteed plus-deviation	921-451

## Packing & Shipping

Delivery time	1 d
Dimensions packaging (W×D×H)	3,5×3,5×3 mm
Shipping method	Parcel service
Net weight approx.	0,05 kg
Gross weight approx.	0,05 kg
Shipping weight	0,1 kg

## Optional cases

Case - Plastic article number	347-009-400
Case - Aluminium article number	317-009-600
Case - Wood article number	338-090-200

## Product information

GTIN/EAN number	4045761240315
Trade number	84239090
REACH classification	no prohibited substances

## Pictograms

### STANDARD



### OPTION

