

# KERN 347-146

Individual weight, OIML Class M1, 10 kg, Hook weight, stainless steel fine turned



## Category

Brand	KERN
Product category	Individual weight
Product group	OIML M1
Product family	347

## Measuring System

Test weight - volume (cm <sup>3</sup> )	1190,4762
Test weight - Density uncertainty (kg/m <sup>3</sup> )	100
Test weight - volume uncertainty (cm <sup>3</sup> )	24,093
Weight OIML class	M1
Test weight - nominal value	10 kg
Permissible tolerance according to OIML (+/-)	500 mg
Test weight - Density (kg/m <sup>3</sup> )	8000
OIML-compliant	✓
Test weight - Density [Min] (OIML)	2600

## Construction

Shape weight	Hook weight
Dimensions (Ø×H)	100×160 mm
Material	stainless steel fine turned
Adjustment method	Adjusting cavity - screwed

## Services (optional)

Article number for DAkkS calibration	962-644
--------------------------------------	---------

## Packing & Shipping

Delivery time	1 d
Dimensions packaging (W×D×H)	100×100×160 mm
Shipping method	Parcel service
Net weight approx.	10 kg
Gross weight approx.	10 kg
Shipping weight	10 kg

## Product information

GTIN/EAN number	4045761475045
Trade number	84239090
REACH classification	no prohibited substances

## Pictograms

### STANDARD



### OPTION

