

KERN 357-01

Individual weight, OIML Class M2, 1 g, Knob, stainless steel fine turned



| | |
|------------------------------|----------------|
| Dimensions packaging (W×D×H) | 24×24×51 mm |
| Shipping method | Parcel service |
| Net weight approx. | 0,05 kg |
| Gross weight approx. | 0,05 kg |
| Shipping weight | 0,1 kg |

Optional cases

| | |
|---------------------------------|-------------|
| Case - Plastic article number | 347-030-400 |
| Case - Aluminium article number | 317-010-600 |
| Case - Wood article number | 337-010-200 |

Product information

| | |
|----------------------|--------------------------|
| GTIN/EAN number | 4045761288836 |
| Trade number | 84239090 |
| REACH classification | no prohibited substances |

Pictograms

STANDARD



OPTION



Category

| | |
|------------------|-------------------|
| Brand | KERN |
| Product category | Individual weight |
| Product group | OIML M2 |
| Product family | 357 |

Measuring System

| | |
|--|--------|
| Test weight - volume (cm ³) | 0,119 |
| Test weight - Density uncertainty (kg/m ³) | 140 |
| Test weight - volume uncertainty (cm ³) | 0,0024 |
| Weight OIML class | M2 |
| Test weight - nominal value | 1 g |
| Permissible tolerance according to OIML (+/-) | 3 mg |
| Test weight - Density (kg/m ³) | 7950 |
| OIML-compliant | ✓ |

Construction

| | |
|-------------------|-----------------------------|
| Shape weight | Knob |
| Dimensions (Ø×H) | 6×6 mm |
| Material | stainless steel fine turned |
| Adjustment method | Polishing |

Services (optional)

| | |
|--------------------------------------|---------|
| Article number for DAkkS calibration | 962-631 |
|--------------------------------------|---------|

Packing & Shipping

| | |
|---------------|-----|
| Delivery time | 1 d |
|---------------|-----|