

KERN 357-04

KERN

Individual weight, OIML Class M2, 10 g, Knob, stainless steel fine turned



Dimensions packaging (W×D×H)	24×24×51 mm
Shipping method	Parcel service
Net weight approx.	0,05 kg
Gross weight approx.	0,05 kg
Shipping weight	0,1 kg

Optional cases

Case - Plastic article number	347-050-400
Case - Aluminium article number	317-040-600
Case - Wood article number	337-040-200

Product information

GTIN/EAN number	4045761288959
Trade number	84239090
REACH classification	no prohibited substances

Pictograms

STANDARD



OPTION



Category

Brand	KERN
Product category	Individual weight
Product group	OIML M2
Product family	357

Measuring System

Test weight - volume (cm ³)	1,1905
Test weight - Density uncertainty (kg/m ³)	140
Test weight - volume uncertainty (cm ³)	0,0241
Weight OIML class	M2
Test weight - nominal value	10 g
Permissible tolerance according to OIML (+/-)	6 mg
Test weight - Density (kg/m ³)	7950
OIML-compliant	✓

Construction

Shape weight	Knob
Dimensions (Ø×H)	10×17,5 mm
Material	stainless steel fine turned
Adjustment method	Polishing

Services (optional)

Article number for DAkks calibration	962-634
--------------------------------------	---------

Packing & Shipping

Delivery time	1 d
---------------	-----