

# KERN 357-08

Individual weight, OIML Class M2, 200 g, Knob, stainless steel fine turned



## Category

Brand	KERN
Product category	Individual weight
Product group	OIML M2
Product family	357

## Measuring System

Test weight - volume (cm <sup>3</sup> )	23,8095
Test weight - Density uncertainty (kg/m <sup>3</sup> )	140
Test weight - volume uncertainty (cm <sup>3</sup> )	0,4819
Weight OIML class	M2
Test weight - nominal value	200 g
Permissible tolerance according to OIML (+/-)	30 mg
Test weight - Density (kg/m <sup>3</sup> )	7950
OIML-compliant	✓
Test weight - Density [Min] (OIML)	2300

## Construction

Shape weight	Knob
Dimensions (Ø×H)	28×47 mm
Material	stainless steel fine turned
Adjustment method	Adjusting cavity - Seal

## Services (optional)

Article number for DAkkS calibration	962-638
--------------------------------------	---------

## Packing & Shipping

Delivery time	1 d
Dimensions packaging (W×D×H)	31×31×56 mm
Shipping method	Parcel service
Net weight approx.	0,20 kg
Gross weight approx.	0,20 kg
Shipping weight	0,2 kg

## Optional cases

Case - Plastic article number	347-080-400
Case - Aluminium article number	317-080-600
Case - Wood article number	337-080-200

## Product information

GTIN/EAN number	4045761289000
Trade number	84239090
REACH classification	no prohibited substances

## Pictograms

### STANDARD



### OPTION

