

# KERN 357-11

Individual weight, OIML Class M2, 1 kg, Knob, stainless steel fine turned



## Packing & Shipping

Delivery time	1 d
Dimensions packaging (W×D×H)	61×61×94 mm
Shipping method	Parcel service
Net weight approx.	1,00 kg
Gross weight approx.	1,00 kg
Shipping weight	1 kg

## Optional cases

Case - Plastic article number	347-110-400
Case - Aluminium article number	317-110-600
Case - Wood article number	337-110-200

## Product information

GTIN/EAN number	4045761289024
Trade number	84239090
REACH classification	no prohibited substances

## Pictograms

### STANDARD



### OPTION



## Category

Brand	KERN
Product category	Individual weight
Product group	OIML M2
Product family	357

## Measuring System

Test weight - volume (cm <sup>3</sup> )	119,0476
Test weight - Density uncertainty (kg/m <sup>3</sup> )	140
Test weight - volume uncertainty (cm <sup>3</sup> )	2,4093
Weight OIML class	M2
Test weight - nominal value	1 kg
Permissible tolerance according to OIML (+/-)	160 mg
Test weight - Density (kg/m <sup>3</sup> )	7950
OIML-compliant	✓
Test weight - Density [Min] (OIML)	2300

## Construction

Shape weight	Knob
Dimensions (Ø×H)	48×80 mm
Material	stainless steel fine turned
Adjustment method	Adjusting cavity - Seal

## Services (optional)

Article number for DAkkS calibration	962-641
--------------------------------------	---------