

SAUTER AD 0027

Jaws with V-grip

KERN



Pictograms

STANDARD



Category

Brand	Sauter
Product category	Measurementtechnology
Product group	Jaws, V-Grip

Construction

Dimension (W×D×H)	30×30×8 mm
Dimension housing (W×D×H)	30×30×8 mm
Dimensions completely mounted (W×D×H)	30×30×8 mm
Material	steel
Material display housing	steel
Maximum clamp width	30 mm
Clamping width	8 mm
Tensile/compressive force [Max]	5 kN

Environmental conditions

Storage temperature [Min]	-10 °C
Storage temperature [Max]	40 °C

Packing & Shipping

Delivery time	14 d
Dimensions packaging (W×D×H)	30×30×8 mm
Shipping method	Parcel service
Net weight approx.	0,30 kg
Gross weight approx.	0,30 kg
Shipping weight	0,28 kg

Product information

GTIN/EAN number	4045761174863
Trade number	90278990
REACH classification	no prohibited substances