

SAUTER AD 0044

Jaws with rubberised surface

KERN



Pictograms

STANDARD



Category

Brand	Sauter
Product category	Measurementtechnology
Product group	Jaws, rubberised

Construction

Dimension (W×D×H)	30×100×8 mm
Dimension housing (W×D×H)	30×100×8 mm
Dimensions completely mounted (W×D×H)	30×100×8 mm
Material	steel, nickel-plated
Material display housing	steel, nickel-plated
Maximum clamp width	100 mm
Clamping width	8 mm
Tensile/compressive force [Max]	5 kN

Environmental conditions

Storage temperature [Min]	-10 °C
Storage temperature [Max]	40 °C

Packing & Shipping

Delivery time	14 d
Dimensions packaging (W×D×H)	30×100×8 mm
Shipping method	Parcel service
Net weight approx.	0,75 kg
Gross weight approx.	0,75 kg
Shipping weight	0,72 kg

Product information

GTIN/EAN number	4045761174993
Trade number	90278990
REACH classification	no prohibited substances