

# SAUTER AD 0058

**KERN**

Jaws with corrugated grip



## Pictograms

STANDARD



### Category

|                  |                       |
|------------------|-----------------------|
| Brand            | Sauter                |
| Product category | Measurementtechnology |
| Product group    | Jaws, corrugated grip |

### Construction

|                                       |                      |
|---------------------------------------|----------------------|
| Dimension (W×D×H)                     | 30×50×8 mm           |
| Dimension housing (W×D×H)             | 30×50×8 mm           |
| Dimensions completely mounted (W×D×H) | 30×50×8 mm           |
| Material                              | steel, nickel-plated |
| Material display housing              | steel, hardened      |
| Maximum clamp width                   | 50 mm                |
| Clamping width                        | 28 mm                |
| Tensile/compressive force [Max]       | 5 kN                 |

### Environmental conditions

|                           |        |
|---------------------------|--------|
| Storage temperature [Min] | -10 °C |
| Storage temperature [Max] | 40 °C  |

### Packing & Shipping

|                              |                |
|------------------------------|----------------|
| Delivery time                | 14 d           |
| Dimensions packaging (W×D×H) | 30×50×8 mm     |
| Shipping method              | Parcel service |
| Net weight approx.           | 0,50 kg        |
| Gross weight approx.         | 0,50 kg        |
| Shipping weight              | 0,5 kg         |

### Product information

|                      |                          |
|----------------------|--------------------------|
| GTIN/EAN number      | 4045761175303            |
| Trade number         | 90278990                 |
| REACH classification | no prohibited substances |