

SAUTER AD 0061

Jaws with rubberised surface

KERN



Pictograms

STANDARD



Category

| | |
|------------------|-----------------------|
| Brand | Sauter |
| Product category | Measurementtechnology |
| Product group | Jaws, rubberised |

Construction

| | |
|---------------------------------------|----------------------|
| Dimension (W×D×H) | 30×80×8 mm |
| Dimension housing (W×D×H) | 30×80×8 mm |
| Dimensions completely mounted (W×D×H) | 30×80×8 mm |
| Material | steel, nickel-plated |
| Material display housing | steel, nickel-plated |
| Maximum clamp width | 80 mm |
| Clamping width | 26 mm |
| Tensile/compressive force [Max] | 10 kN |

Environmental conditions

| | |
|---------------------------|--------|
| Storage temperature [Min] | -10 °C |
| Storage temperature [Max] | 40 °C |

Packing & Shipping

| | |
|------------------------------|----------------|
| Delivery time | 14 d |
| Dimensions packaging (W×D×H) | 30×80×8 mm |
| Shipping method | Parcel service |
| Net weight approx. | 0,50 kg |
| Gross weight approx. | 0,50 kg |
| Shipping weight | 0,5 kg |

Product information

| | |
|----------------------|--------------------------|
| GTIN/EAN number | 4045761175334 |
| Trade number | 90278990 |
| REACH classification | no prohibited substances |