


SAUTER AD 9033

KERN

Screw Tension Clamp for laboratory tensile force measurements



Pictograms

STANDARD



Category

Brand	Sauter
Product category	Clamp
Product group	Screw tension clamp

Construction

Dimensions completely mounted (W×D×H)	160×75×30 mm
Material	aluminium
Mounting - force dissipation	Threaded hole M6 External thread M12
Maximum clamp width	100 mm
Clamping width	52 mm
Tensile/compressive force [Max]	1 kN

Environmental conditions

Storage temperature [Min]	-10 °C
Storage temperature [Max]	40 °C

Packing & Shipping

Delivery time	14 d
Dimensions packaging (W×D×H)	160×75×30 mm
Shipping method	Parcel service
Net weight approx.	1,2 kg
Gross weight approx.	1,2 kg
Shipping weight	1,04 kg

Product information

GTIN/EAN number	4045761178427
Trade number	90278990
REACH classification	no prohibited substances