

SAUTER AD 9120

KERN

Rope and thread tension clamp up to 1 kN, Aluminium



Pictograms

STANDARD



Category

Brand	Sauter
Product category	Clamp
Product group	Rope and thread tension clamp

Construction

Dimensions completely mounted (W×D×H)	90×72×35 mm
Material	aluminium
Mounting - force dissipation	Threaded hole M6 External thread M12
Maximum clamp width	8 mm
Clamping width	2 mm
Tensile/compressive force [Max]	1 kN

Environmental conditions

Storage temperature [Min]	-10 °C
Storage temperature [Max]	40 °C

Packing & Shipping

Delivery time	14 d
Dimensions packaging (W×D×H)	90×72×35 mm
Shipping method	Parcel service
Net weight approx.	0,25 kg
Gross weight approx.	0,25 kg
Shipping weight	0,25 kg

Product information

GTIN/EAN number	4045761178540
Trade number	90278990
REACH classification	no prohibited substances