

KERN FH 2KUK



Universal digital force gauge for tensile and compressive force measurements with external load cell, with plug-in power supply for UK



Functions

| | |
|--|-----------------|
| Auto-off interval(s) in battery mode/rechargeable battery mode | 1 - 60 min |
| Peak function | ✓ |
| Statistic function | ✓ |
| Limit-setting function | ✓ |
| Memory function | ✓ |
| Interfaces | RS-232 standard |

Power Supply

| | |
|---|------------------------|
| Input voltage power supply / power [Max] | 100 V - 240 V |
| Input voltage device / power [Max] | 12 V, 400 mA |
| Plug-in power supply type | Power adapter |
| Supplied plug-in power supply | Battery & Power supply |
| Plug-in power supply / adapter for countries - included with the delivery | UK |
| Rechargeable battery | 8,4V / 1200mAh Ni-Hi |
| Rechargeable battery charging time | 4 h |
| Rechargeable battery operating time - backlight on | 10 h |
| Rechargeable battery operating time - backlight off | 12 h |

Environmental conditions

| | |
|---------------------------|-------|
| Ambient temperature [Min] | 10 °C |
| Ambient temperature [Max] | 40 °C |

Packing & Shipping

| | |
|------------------------------|----------------|
| Readability force [d] (N) | 1 d |
| Shipping method | Parcel service |
| Dimensions packaging (W×D×H) | 325×185×165 mm |
| Net weight approx. | 1,6 kg |
| Gross weight approx. | 2,8 kg |
| Shipping weight | 2,734 kg |
| UN number (hazardous goods) | 3496 |

Services (optional)

| | |
|--|---------|
| Article number for factory calibration (tensile force) | 961-162 |
| Article number for factory calibration (compressive force) | 961-262 |
| Article number for factory calibration (tensile force/compressive force) | 961-362 |

Category

| | |
|------------------|---------------------|
| Brand | Sauter |
| Product category | Force gauges |
| Product group | Digital force gauge |

Measuring System

| | |
|------------------------------------|-----------|
| Readability force [d] (N) | 1 N |
| Overload protection (% of [Max]) | 150% |
| Measuring range [Max] (N) | 2 kN |
| Tolerance (% of [Max]) | 0,5% |
| Default unit | kN |
| Measuring head measuring frequency | 2 kHz |
| Directions of force | pull push |

Approval

| | |
|---------|---|
| CE mark | ✓ |
|---------|---|

Display

| | |
|----------------------|-------|
| Display digit height | 10 mm |
| Screen reversible | ✓ |

Construction

| | |
|---------------------------------------|--------------|
| Dimension display device (W×D×H) | 230×66×36 mm |
| Dimension housing (W×D×H) | 230×66×36 mm |
| Dimensions completely mounted (W×D×H) | 230×66×36 mm |
| Material display housing | Plastics |
| Cable length | 3 m |
| Load support (tensile force) | Rod end |

KERN FH 2KUK



Universal digital force gauge for tensile and compressive force measurements with external load cell, with plug-in power supply for UK

Piktogramme

STANDARD



OPTION

