

SAUTER HED 100

KERN

Shore hardness tester with extensive functionality



Category

Brand	Sauter
Product category	Hardness testing
Product group	Digital Shore hardness tester
Product family	HE

Measuring System

Readability hardness [d] (Shore)	0,1
Measuring range Shore	100
Test object thickness [Min]	6 mm
Hardness scales	Shore D
Leeb Hardness Tester sensor type	D
Units	HD
Tolerance (% of [Max])	1%
Test force Hardness measurement	50 N
Measuring probe diameter	18 mm

Display

Display type	LCD
Display screen size	32×21 mm

Construction

Dimension (W×D×H)	153×50×29 mm
Dimension housing (W×D×H)	153×50×29 mm
Material housing	plastic

Functions

Function for averaging	✓
Limit-setting function	✓
Hold function	✓
Peak function	✓

Memory function	✓
Memory - number of results	500
Statistic function	✓
Auto-off interval(s) in battery mode/rechargeable battery mode	2 min

Interface

Interfaces	USB-Device
------------	------------

Power Supply

Supplied power supply	Accu & Power supply
Power supply type	Power adapter
Plug-in power supply / adapter for countries - included with the delivery	EURO
Plug-in power supply / adapter for countries - optional	UK
Input voltage power supply / power [Max]	100 V - 240 V, 50 / 60 Hz
Power supply cable removable	removable
Input voltage device / power [Max]	5 V 1000 mA
Power socket for mains adapter	Inside plus, outside minus
Battery / accumulator type	NiMH
Battery connection	Connector pin
Battery operating time - backlight off	20 h
Battery operating time	20 h
Battery capacity	400 mAh
Battery voltage	3,6 V
Battery - Number of cells	3
Battery - Individual weight	42 g
Battery - Total weight	126 g
Battery - Construction	Inseparable connection of cells (pack)
Rechargeable battery operating time - backlight on	20 h
Rechargeable battery operating time - backlight off	20 h
Rechargeable battery charging time	3 h

Approval

CE mark	✓
---------	---

Packing & Shipping

Delivery time	1 d
Dimensions packaging (W×D×H)	295×165×115 mm

SAUTER HED 100



Shore hardness tester with extensive functionality

Shipping method	Parcel service
Net weight approx.	0,20 kg
Gross weight approx.	0,80 kg
Shipping weight	1,1 kg

Product information

GTIN/EAN number	404576 1274020
Trade number	90248000
REACH classification	no prohibited substances

Pictograms

STANDARD

