

# KERN KDE-T

Multi-function model, protected to IP65

# KERN



## Category

Brand	KERN
Product category	Measuring Technology Components
Product group	Display devices

## Measuring System

Number of weighing ranges	2
Linearisation in dots	4
Units	kg g lb oz
Default unit	kg
Adjustment options	Adjusting with external weight
Terminal resolution (not verifiable)	20.000

## Approval

CE mark	✓
---------	---

## Display

Display type	LCD with backlight
Display digit height	25 mm
Display backlight	✓

## Construction

Dimension housing (W×D×H)	225×110×45 mm
Material display housing	Plastics

## Functions

Auto-off interval(s) in battery mode/rechargeable battery mode	selectable
Time display	✓
PreTare function	✓
Tare function	manual (multi)

Hold function	✓
Percentage determination	✓
Counting function	✓
Function for averaging under unstable weighing conditions	✓
Recipe/summing level	Rez A (Net total)
Interfaces	RS-232 standard

## Counting

Reference quantity	5, 10, 20, 25, 50
--------------------	-------------------

## Power Supply

Input voltage power supply / power [Max]	100 V - 240 V, 50 / 60 Hz
Input voltage device / power [Max]	15 V, 500 mA
Plug-in power supply type	Power adapter
Supplied plug-in power supply	Power supply unit
Plug-in power supply / adapter for countries - included with the delivery	EURO UK US CH
Plug-in power supply / adapter for countries - optional	EURO UK US CH
Rechargeable battery optional	Rchrg. battery optional - intern
Rechargeable battery	NDE-A02
Rechargeable battery charging time	10 h
Rechargeable battery operating time - backlight on	10 h
Rechargeable battery operating time - backlight off	15 h
Battery	9 V block
Battery operating time	24 h

## Environmental conditions

Humidity of environment [Max]	80 %
Ambient temperature [Min]	5 °C
Ambient temperature [Max]	35 °C

## Packing & Shipping

Readability force [d] (N)	1 d
Shipping method	Parcel service
Dimensions packaging (W×D×H)	205×270×70 mm
Net weight approx.	0,70 kg
Gross weight approx.	1,00 kg
Shipping weight	1 kg

# KERN KDE-T



Multi-function model, protected to IP65

## Services (optional)

Article number for adjustment at the location of installation    auf Anfrage | on request

## Piktogramme

### STANDARD



### OPTION

