

KERN KDE-TH

Multi-function model, protected to IP65

KERN



PreTare function	✓
Tare function	manual (multi)
Hold function	✓
Percentage determination	✓
Counting function	✓
Function for averaging under unstable weighing conditions	✓
Recipe/summing level	Rez A (Net total)
Interfaces	RS-232 standard
IP protection - complete device	IP65

Power Supply

Input voltage power supply / power [Max]	100 V - 240 V, 50 / 60 Hz
Input voltage device / power [Max]	15 V, 600 mA
Plug-in power supply type	Power adapter
Supplied plug-in power supply	Power supply unit
Plug-in power supply / adapter for countries - included with the delivery	EURO UK US CH
Plug-in power supply / adapter for countries - optional	EURO UK US CH
Rechargeable battery optional	Rchrg. battery optional - intern
Rechargeable battery	NDE-A02
Rechargeable battery charging time	10 h
Rechargeable battery operating time - backlight on	10 h
Rechargeable battery operating time - backlight off	15 h
Battery	9 V block
Battery operating time	24 h

Environmental conditions

Humidity of environment [Max]	80 %
Ambient temperature [Min]	5 °C
Ambient temperature [Max]	35 °C

Packing & Shipping

Readability force [d] (N)	1 d
Shipping method	Parcel service
Dimensions packaging (W×D×H)	260×170×150 mm
Net weight approx.	1,00 kg
Gross weight approx.	1,00 kg
Shipping weight	1,3 kg

Category

Brand	KERN
Product category	Measuring Technology Components
Product group	Display devices

Measuring System

Number of weighing ranges	2
Linearisation in dots	3
Units	kg g lb oz ffa
Default unit	kg
Adjustment options	Adjusting with external weight
Terminal resolution (not verifiable)	35.000

Approval

CE mark	✓
---------	---

Display

Display type	LCD with backlight
Display digit height	25 mm
Display backlight	✓

Construction

Dimension housing (W×D×H)	225×110×45 mm
Material display housing	Plastics
Display device cable length	1,5 m

Functions

Auto-off interval(s) in battery mode/rechargeable battery mode	selectable
Time display	✓

KERN KDE-TH



Multi-function model, protected to IP65

Services (optional)

Article number for adjustment at the location of installation auf Anfrage | on request

Piktogramme

STANDARD



OPTION

