

KERN MBC-A01

KERN

Mechanical height rod to fix to the scale, measuring range 10 cm–80 cm, increments of 1 mm



Shipping weight 4,5 kg

Piktogramme

STANDARD



Category

Brand	KERN
Product category	Balances
Product group	Height rods

Measuring System

Readability length [d]	1 mm
Measuring range length [Max]	80 cm
Measuring range length [Min]	10 cm
Tolerance measuring rod	5 mm
Linearity	±
Units	inch inch/ft cm
Measuring range measuring rod (cm)	10-80cm @ 0,1cm ± 0,5cm

Approval

CE mark	✓
Approval according to 93/42/EEC (med.)	✓

Construction

Dimension housing (W×D×H)	900×465×180 mm
Material housing	plastic

Environmental conditions

Humidity of environment [Max]	80 %
Ambient temperature [Min]	0 °C
Ambient temperature [Max]	40 °C

Packing & Shipping

Readability force [d] (N)	1 d
Shipping method	Parcel service
Dimensions packaging (W×D×H)	180×890×140 mm
Net weight approx.	0,80 kg
Gross weight approx.	1,4 kg